



adorne Collection
Discontinued - adorne® 1100W Incandescent/Halogen sofTap® Dimmer, Magnesium
Part No. ADTP1103HM4



Control your lights, and even adjust the light level, with just a soft tap of a finger thanks to inventive micro-movement technology. Use this dimmer switch on its own to control an incandescent or halogen light or fixture from a single location, or pair with another remote dimmer switch for 3-way control a single light source from two locations.

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable incandescent/halogen bulbs or fixtures. Perfect for adding precise light level control -- all it takes is a soft tap to turn on/off or adjust brightness.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	ADTP703TUM4
Color	Magnesium	Country Of Origin	China
Features	Indicator Lights	Switch Type	sofTap
Number of Switches	1	Standard	cULus
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Dimensions

Product Width US	2.51 in	Product Depth US	1.79 in
------------------	---------	------------------	---------

Product Height US4.2 in

Technical Information

Electrical Rating	120V 700W (Halogen), 120V 700W (Incandescent)	Connection	Screw Terminals
Number of Gangs	1	Bulb Compatibility	Halogen, Incandescent
Number of Poles	3-Way, Single Pole	Wattage	1100 W
Mounting Type	Box	Voltage	120.0 V
Load	Incandescent, Halogen		