



adorne Collection

Discontinued - adorne® sofTap™ Wi-Fi Ready Master Incandescent / Halogen Dimmer, Magnesium
Part No. ADTP600RMHM1



The sofTap Wi-Fi Ready Master Dimmer is a programmable light switch and dimmer combination that pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Manually turn lights on/off or adjust their brightness with the soft tap of a finger, or enjoy mobile control and create custom lighting scenes to control lights through the Legrand Lighting Control app for smartphones or tablets. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.



Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Pair with a sofTap Wi-Fi Ready Remote Dimmer for 3-way control. Simply follow the provided instructions after installing to pair with the Master Dimmer. For use with incandescent/halogen bulbs.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Country Of Origin	United States	Features	Indicator Lights, Smart Lighting
Switch Type	sofTap	Number of Switches	1
Works With	Amazon Alexa, Google Assistant, Radio Frequency	Application Sector	Residential
Standard	cULus, FCC, UL 1472	Warranty Type	2-Year Limited Warranty

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Frequency Rating	900 M (RF) Hz	Number of Gangs	1
Amperage	5.5 A	Bulb Compatibility	Halogen, Incandescent
Number of Poles	3-Way, Multi-Location, Single Pole	Wattage	600 W
Mounting Type	Box	Voltage	120.0 V
Connection Type	Internal Pressure Plates	Load	Halogen, Incandescent
Environmental Conditions	0 to 80% (relative humidity, non-condensing)		