



adore Collection
Discontinued - adore® 700W Incandescent/Halogen sofTap® Dimmer, Magnesium
Part No. ADTP703HM2



Turn lights on/off, or even dim them, with just a soft tap of a finger thanks to inventive micro-movement technology. This dimmer switch is meant for use with incandescent or halogen single fixtures and small lighting groups that do not exceed 700W. Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adore® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

For use with dimmable incandescent/halogen bulbs or fixtures that do not exceed 700W. Perfect for adding precise light level control -- all it takes is a soft tap to turn on/off or adjust brightness.

Usable in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	ADTP703TUM4
Color	Magnesium	UPC Number	785007023367
Country Of Origin	China	Features	Indicator Lights
Switch Type	sofTap	Number of Switches	1
Standard	cULus	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

Technical Information

Connection	Screw Terminals	Number of Gangs	1
Bulb Compatibility	Halogen, Incandescent	Number of Poles	3-Way, Single Pole

Wattage	700 W	Mounting Type	Box
Connection Type	Internal Pressure Plates		