



adore Collection  
adore® 700W sofTap® Tru-Universal Dimmer, White, with Microban®  
Part No. ADTP703TUW4



Turn lights on or off, or even dim them, with just a soft tap of a finger thanks to inventive micro-movement technology. Plus, as a Tru-Universal Dimmer, this dimmer switch self-calibrates to work with virtually any 120V dimmable bulb or fixture (excludes 0-10V). Always adjust to the precise light level you want, without the flicker.

This dimmer\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adore® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required.

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adore® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Perfect for adding precise light level control – all it takes is a soft tap to turn on/off or adjust brightness.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Features	Antimicrobial Protection, Indicator Lights	Switch Type	sofTap
Number of Switches	1	Application Sector	Residential

Warranty Type	Limited Lifetime Warranty	Type	Dimmer
Dimensions			
Product Width US	1.79 in	Product Depth US	1.77 in
Product Height US	4.2 in		
Technical Information			
Electrical Rating	120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent), 120V 8A (EFL)	Connection	Screw Terminals
Number of Gangs	1	Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon
Number of Poles	Single Pole 3-Way	Indoor/Outdoor	Indoor
Wattage	700 W	Mounting Type	Box
Voltage	120.0 V	Connection Type	Internal Pressure Plates