



adorne Collection
Discontinued - adorne® Whisper Wi-Fi Ready Remote Dimmer, Magnesium
Part No. ADWRRRM1



Working in conjunction with an adorne Hub and a Whisper Wi-Fi Ready Master Dimmer for 3-way control. Use the dimmer to turn lights on/off, or adjust brightness, all with just a fluid, whisper-soft motion. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes. Installs in 25 minutes or less.

Allows 3-way application when paired with a Wi-Fi Ready Master Dimmer, letting you control a light or fixture from an additional location without running new wires. Pair with the Wi-Fi Ready Master Dimmer via the easy-to-follow instructions. Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems. Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Country Of Origin	China	Features	Indicator Lights, Smart Lighting
Switch Type	Whisper	Number of Switches	1
Works With	Amazon Alexa, Control4, Elan, Google Assistant, Radio Frequency, RTI, URC	Application Sector	Residential
Standard	UL, FCC, cULus, RoHS	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	4.2 in	Product Depth US	1.79 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Conformant	Yes		
-----------------	-----	--	--

Technical Information

Electrical Rating	120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL)	Frequency Rating	900 Hz
Number of Gangs	1	Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon
Number of Poles	3-Way, Multi-Location, Single Pole	Mounting Type	Box
Voltage	120.0 V	Connection Type	Internal Pressure Plates
Environmental Conditions	0 to 80% (relative humidity, non-condensing)		