



Wiremold  
5' Alternating USB Aluminum Plugmold® Multioutlet System  
Part No. AL20GB509TRUSBA



Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 USB Plugmold THHN (1 hot, 1 neutral and insulated ground conductor). .040" (1.0 mm) aluminum housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amps (shared between two ports) 5VDC. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

## Features & Benefits

USB charging. Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.

Compact design. Low-profile design installs in tight locations while offering multiple power and USB charging connections. Receptacle spacing accommodates bulky AC adapters.

Tamper-resistant receptacles. Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776184426
Country Of Origin	United States	Number of Receptacles	6
Application Sector	Commercial	Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT
Type	Plugmold		

### Dimensions

Product Width US	1.42 in	Product Depth US	1.13 in
Product Length US	1.42 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA Yes

Additional Information

RoHS Conformant Yes Product Environmental Profile Yes

Technical Information

Frequency Rating 60 Hz Amperage 20 A

Enclosure Type Aluminum Voltage 125.0 V

Environmental Conditions Dry interior locations