



Wiremold
AMTC-415 - AMTC-4 Series Vertical Drop Aluminum Pole
 Part No. AMTC-415



Two-compartment pole. Nominal material thickness .050" (1.8mm). Length: 15' 5" (4.7m). Furnished unwired without outlets. Two 8" (203mm) removable covers with KOs for modular jacks and modular furniture communication outlets. Mounting hardware, entrance end plate and ceiling trim plates furnished. NOTE: Custom options - features such as colors or other lengths (20' (6.1m) maximum) available on custom orders.

Features & Benefits

Two-compartment pole. Nominal material thickness .050" (1.8mm). Length: 15' 5" (4.7m). Furnished unwired without outlets. Two 8" (203mm) removable covers with KOs for modular jacks and modular furniture communication outlets. Mounting hardware, entrance end plate and ceiling trim plates furnished. NOTE: Custom options - features such as colors or other lengths (20' (6.1m) maximum) available on custom orders.

Specifications

General Info

| | | | |
|-------------------|---------------|------------|--|
| Product Line | Wiremold | UPC Number | 786776046496 |
| Country Of Origin | United States | Standard | cULus Listed Multioutlet Assemblies: File E15191 E178348 Guide PVGT, Raceway Fittings: File E41751 Guide RJPR, Accessories: File E53857 Guide RVUR Meets Article 380 & 386 of NEC |

Dimensions

| | | | |
|------------------|----------|-------------------|-----------|
| Product Width US | 2.312 in | Product Height US | 185.04 in |
|------------------|----------|-------------------|-----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E15191 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Buy American Act Compliance

| | |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

| | | | |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|
