



adorne Collection  
Discontinued - adorne® 27-in Modular Track  
Part No. APMT27TM2



A base under-cabinet modular track for use as the foundation of an adorne Under-Cabinet Lighting and Power System. Easily eliminate countertop clutter while also creating a more functional space within your kitchen. With its customizable modular design, you can create a unique under-cab solution that perfectly fits your home and needs. Modular tracks also available in 12 inch and 18 inch lengths. All lengths available in white or titanium finish.

## Features & Benefits

|   |   |
|---|---|
| Perfect for eliminating countertop clutter and creating a more functional kitchen counter space                                 | An under-cabinet base that allows you to add or change out modules with ease                                      |
| The 27 inch Modular Track includes one outlet module and one blank module, and can support up to two Linear LED Lights          | The adorne 27 inch Modular Track must be installed with an adorne Control Box                                     |
| Module options include standard and USB outlets, our Digital Music Kit and smart device cradles to eliminate countertop clutter | Installs in 30 minutes or less. Mounts to the wall underneath kitchen cabinets. All required hardware is provided |
| Pair with other modular tracks to create a full system custom-designed for your kitchen   | Modular Tracks available in various sizes, and plug seamlessly together for easy installation                     |

## Specifications

### General Info

|                   |  |                    |             |
|-------------------|--|--------------------|-------------|
| Product Line      | Pass & Seymour                                 | Color              | Titanium    |
| Country Of Origin | Mexico   | Application Sector | Residential |
| Standard          | NONMETALLIC RACEWAY LISTED TO UL 5A, CSA C22.2 |                    |             |

### Technical Information

|                  |        |          |         |
|------------------|--------|----------|---------|
| Frequency Rating | 60 Hz  | Amperage | 20 A    |
| Wattage          | 2400 W | Voltage  | 125.0 V |