



adorne Collection
Discontinued - adorne® USB Outlet - Half-Size, Graphite
Part No. ARUSBG4



Get a full battery for your phones, tablets and more with the convenience of built-in charging. Features one USB Type-A connection. Pair with another half or standard-sized device to fill an adorne One-Gang or One-Gang+ Wall Plate. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Provides convenient built-in charging, without sacrificing a plug requiring a bulky adapter.

Pairs with any other half-sized device to fit an adorne 1-Gang Wall Plate.

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-------------------|-----------------------------------|-------------------------|---------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | ARUSBM4 |
| Color | Graphite | Finish | Graphite |
| Country Of Origin | China | Features | USB-A Charging |
| Outlet Type | Indoor, Residential, USB-Charging | Warranty Type | Limited Lifetime Warranty |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.81 in | Product Depth US | 0.89 in |
| Product Height US | 1.77 in | | |

Technical Information

| | | | |
|------------------|--------------------------|--------------------------|---|
| USB Amperage | 2.1 A | Connection | Side and Back Wire |
| Number of USBs | 1 | Number of Gangs | 1 |
| USB Power Output | 11 W | Amperage | 15 A |
| Indoor/Outdoor | Indoor | Wattage | 11 W |
| Mounting Type | Box | Voltage | 125.0 V |
| Connection Type | Internal Pressure Plates | Environmental Conditions | 95% (relative humidity, non-condensing) |