



adorne Collection
Discontinued - adorne® Whisper™ Wi-Fi Ready Master Switch, Magnesium
Part No. ASWR155RMM1



The Whisper Wi-Fi Ready Master Switch pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Manually turn lights on/off with a light fluid motion at the wall, or enjoy mobile control and create custom lighting scenes to control lights through the Legrand Lighting Control app for smartphones or tablets. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light. Pair with a Whisper Wi-Fi Ready Remote Switch for 3-way control.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate. More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Country Of Origin	China	Features	Smart Lighting
Switch Type	Whisper	Number of Switches	1
Works With	Amazon Alexa, Google Assistant, Radio Frequency	Application Sector	Residential
Standard	UL, FCC, cULus, RoHS	Warranty Type	1-Year Limited Warranty

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Number of Gangs	1	Number of Poles	4-Way, Multi-Location, Single Pole
Mounting Type	Box	Supply Voltage	120 V
Voltage	120.0 V	Connection Type	Internal Pressure Plates
Environmental Conditions	0 to 80% (relative humidity, non-condensing)		