



adorne Collection
adorne® Graphite Three-Gang Screwless Wall Plate with Microban®
Part No. AWP3GGR4



Dark, handsome and a little bit mysterious, it is perfect for adding on-trend edge to any space. Made exclusively for use with designer switches and outlets from the adorne® Collection. This wall plate* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product. * Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology.

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Made to exclusively fit the designer switches, dimmers and outlets from the adorne® Collection, snapping into place with ease.

Coordinate with other designer switches and outlets throughout your home for a cohesive, contemporary look.

Includes one Wall Plate and one Steel Frame for mounting the wall plate.

A perfect finishing touch for any space, adding a sleek and contemporary aesthetic through its screwless design and low-profile.

Other Wall Plates from the adorne® Collection are available in extensive range of on-trend colors, materials and cast metals.

Specifications

General Info

Product Line	Pass & Seymour	Color	Graphite
Country Of Origin	Mexico	Construction	Screwless Design Snaps into Frame
Features	Antimicrobial Protection	Wall Plate Type	Dimmer/Switch, Outlet
Application Sector	Residential/Commercial	Standard	cULus UL514, cETLus
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	7.06 in	Product Depth US	0.35 in
------------------	---------	------------------	---------

Product Height US	5.13 in
-------------------	---------

Technical Information

Cutout	Rectangular	Thickness	0.07 in
Number of Gangs	3	Mounting Type	Screwless
Orientation	Horizontal	Connection Type	Screwless