

Cord GripMale Straight 2 1/2-inch, 2.062-2.187.



Features & Benefits

Deluxe cord grips are woven of stainless steel mesh with an aluminum body for corrosion resistance.

They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain.

They are recommended for indoor or outdoor use where subjected to moisture in the wiring of pendant stations, processing equipment, hand tools, and extension cord sets.

Deluxe grips are suitable for use in hazardous locations per Class I, Div. 2: Class II, Div. 1 & 2: and Class III, Div. 1 & 2.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Technical Information

Maximum Cable Range	2.062 in	Minimum Cable Range	2.187 in
---------------------	----------	---------------------	----------

Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.		