



Pass and Seymour
Discontinued - Nylon Cord Grip, 1/2-in NPT Straight, Oval UF Cable, .218-.421 OD Range
Part No. CGN5042UF



Features & Benefits

Heavy duty Nylon body is resistant to impact and corrosion

Rubber grommet provides a liquid-tight seal and reduces cord pull-out while resisting chemicals

Available in straight, 90°, and underground feed styles

Color coded grommets make for easy identification and ease of installation

Rugged construction suitable for various industrial applications such as MRO, food processing, water/waste water, marine, pulp & paper, and petrochemical

Specifications

General Info

| | | | |
|--------------|-----------------|--------------------|-----------------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Nylon Cord Grip | Application Sector | Commercial/Industrial |
| Standard | UL Listed | | |

Listing Agencies / 3rd Party Agencies

| | |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

Technical Information

| | | | |
|---------------------|----------|---------------------|----------|
| Maximum Cable Range | 0.218 in | Minimum Cable Range | 0.421 in |
|---------------------|----------|---------------------|----------|