



- Commercial grade corrosion-resistant, plated-steel outlet strap built for heavy-duty use.

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly	.032 inch thick, brass, triple-wipe power contacts for lasting retention
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring	Impact-resistant nylon face and thermoplastic back body
Accepts 14 to 10 AWG solid or stranded copper or copper-clad wire	Terminal compartments isolated from each other for positive conductor containment
Tri-drive terminal and mounting screws	Auto-ground clip assures positive ground
Posted, ready-to-wire terminal screws for added productivity	

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	Country Of Origin	Mexico
Receptacle Type	Double	Number of Receptacles	2
Construction	Nylon face with impact-resistant thermoplastic back body	Outlet Type	Commercial
Application Sector	Commercial	Standard	UL, CSA
Type	Corrosion Resistant, Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Voltage	125.0 V	Connection Type	Wired
Environmental Conditions	90% (relative humidity, non-condensing)		
