



- Commercial grade corrosion-resistant, plated-steel outlet strap built for heavy-duty use.

## Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly	.032 inch thick, brass, triple-wipe power contacts for lasting retention
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring	Impact-resistant nylon face and thermoplastic back body
Accepts 14 to 10 AWG solid or stranded copper or copper-clad wire	Terminal compartments isolated from each other for positive conductor containment
Tri-drive terminal and mounting screws	Auto-ground clip assures positive ground
Posted, ready-to-wire terminal screws for added productivity	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	Country Of Origin	Mexico
Receptacle Type	Double	Number of Receptacles	2
Construction	Nylon face with impact-resistant thermoplastic back body	Standard	UL, CSA
Type	Corrosion Resistant, Outlet		

### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

---

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Voltage	125.0 V	Connection Type	Wired
Environmental Conditions	90% (relative humidity, non-condensing)		

---