



Wiremold
Field Wired deQuorum Single Flip Up Unit with USB
Part No. DQFF15UBK



Field wired unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Comes with a black powder coat finish.

Features & Benefits

Sleek, Attractive Design: Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

Tamper-Resistant Receptacles: Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

New Soft Opening Cover Mechanism: Opening and closing the cover is quieter and easier with a more professional feel.

Expanded Configuration Options: Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

UL Spill Water Protection: Meets or exceeds UL 111 - Outline of Investigation for Multioutlet Assemblies. Eliminates risk of shock or short circuiting due to moisture entering device.

USB Charging Capability: Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

Multiple Cover Finish Options: Durable black powder coat and brushed stainless steel finishes blend with most decors.

cULus Listed: Meets UL US and Canadian Safety standards for Multioutlet Assemblies (File E15191, Guide PVGT).

Specifications

General Info

Product Line	Wiremold	UPC Number	786776186802
Country Of Origin	Mexico	Construction	Various
Application Sector	Commercial	Standard	cULus Multioutlet Assembly File E15191 Guide PVGT Listed to US and Canadian Safety Standards. Meets Article 390 of the NEC.
Type	Flip Up		

Dimensions

Product Width US	4.75 in	Product Length US	5.625 in
Knockout Size	1/2 in	Cubic Capacity	50.19 cu in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Buy American Act Compliance			
NAFTA	Yes		
Additional Information			
RoHS Conformant	Yes		
Technical Information			
Cable Entry	Bottom	Mounting Type	Recessed
Number of Outlets	2		