



Wattstopper
Dual Tech Occupancy Sensor 100 -347 VAC, center mount 360°
Part No. DT-355



Wattstopper's low profile DT-355 dual technology occupancy sensor combines the benefits of passive infrared (PIR) and ultrasonic technologies. The sensor mounts on the ceiling with a flat, unobtrusive appearance and provides 360 degrees of coverage.

Features & Benefits

Architecturally appealing low profile appearance

Ultrasonic diffusers give more comprehensive coverage

Operates at 120, 230 (single phase), 277 or 347 VAC, 50/60 Hz

Terminal wiring for quick and easy installation

Walk-through mode increases savings potential

Specifications

General Info

Product Line	Wattstopper	UPC Number	754182913848
Country Of Origin	China	Features	Indicator Lights, IR (Infrared), Motion Sensor
Application Sector	Commercial	Warranty Type	5-Year

Dimensions

Product Width US	4.0 in	Product Weight US	0.45 lb
Product Volume US	71.25 cu in	Product Depth US	5.0 in
Product Height US	3.0 in		

Additional Information

RoHS Conformant	Yes	DesignLights Consortium Qualified System	Yes
Security	Yes	Product Environmental Profile	Yes
Technical Information			
Sensor Type	Occupancy	Indicator	LED Light
Wattage	800 W	Sensing Range	360 degrees,1000 sq ft
Voltage	100 to 347 V	Connection Type	Wired