



Pass and Seymour
Tamper-Resistant Floor Box Assembly - One Gang for Wood Sub-Floors, Nickel
Part No. FB1TRDRN



Tamper-Resistant Floor Box Assembly, #8 duplex opening. Two threaded screw plugs, Includes 3232 15A, 125A tamper-resistant receptacle. Brass.

Features & Benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Meets UL514(c) and NEC 314.27(c).
- With durable nickel or brass cover plates.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.
- Rugged diecast cover plates.
- Scrub water compliant.
- Dual-voltage models available.
- Wood sub-floors only.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Standard	Residential/Commercial		

Dimensions

Cubic Capacity	20.5 cu in
----------------	------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Outlets	1
---------------------	-----	-------------------	---