



Standard-duty, Closed mesh, Locking bale grips (universal eye). Cable diameter - 0.620-0.740", Bale length - 18", Mesh length - 11", Break strength - 1,150lbs.

## Features & Benefits

Standard closed mesh support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Closed mesh support grips are used when the end of the cable is accessible.

Support grips are woven of corrosion-resistant tinned-bronze wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

## Specifications

### General Info

UPC Number 785007980011

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Construction Various Types of Pulling, Support and Strain Relief Grips

Standard UL/CSA Approval (consult factory)

### Listing Agencies / 3rd Party Agencies

CSA Listed Yes

CSA File Number 67507

### Technical Information

Mounting Consult the Factory for Mounting Recommendations

Cable Size Cable Dia. Range: 0.620-0.740; Bale Length: 18; Mesh Length: 11

Capacity Various Cable Diameter Ranges

---

**Load**

Approx. Break Strength: 1,150

---