

Standard duty, Closed mesh, Locking bale grips (universal eye). Cable diameter - 0.750-0.990", Bale length - 18", Mesh length - 14", Break strength - 1,320 lbs.



## Features & Benefits

Standard closed mesh support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Closed mesh support grips are used when the end of the cable is accessible.

Support grips are woven of corrosion-resistant tinned-bronze wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

## Specifications

### General Info

**UPC Number** 785007980028

**Countries Of Origin** Mexico

**Product Line** Pass & Seymour

**Application Sector** Industrial

**Construction** Various Types of Pulling, Support and Strain Relief Grips

**Standard** UL/CSA Approval (consult factory)

### Listing Agencies / 3rd Party Agencies

**CSA Listed** Yes

**CSA File Number** 67507

### Technical Information

**Mounting** Consult the Factory for Mounting Recommendations

**Cable Size** Cable Dia. Range: 0.750-0.990; Bale Length: 18; Mesh Length: 14

**Capacity** Various Cable Diameter Ranges

---

**Load**

Approx. Break Strength: 1,320

---