




FC250UU: Standard Duty, Closed Mesh, Double -Eye Grip, Cable Diameter 2.50 - 2.99 inches, Bale Length 6-in, Mesh Length 24-in, Break Strength 3360 lbs.



Features & Benefits

Closed mesh support grips are used when the end of the cable is accessible.	Standard duty closed mesh support grips are designed for loads up to 600 lbs.
Vertical runs of no more than 100 ft.	They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
Support grips are woven of corrosion-resistant tinned-stainless steel wire.	Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.
Bale Length: 6: Mesh Length: 24	

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Maximum Cable Range	2.5 in	Minimum Cable Range	2.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 3360		