



Isolated Ground Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

Face color coding by voltage facilitates locating and mating of proper devices.

High-impact resistant nylon face resists impacts and scrapes.

Corrosion-resistant plated steel strap.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-------------------|--------------------|-------------------------|-----------|
| Product Line | Pass & Seymour | Replaced by Part Number | IG26362LA |
| Color | Light Almond | Finish | Matte |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Commercial, Indoor | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.322 in | Product Depth US | 0.833 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|----------------|--------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |