



Wiremold  
Rack Mount 120V/15A/6 rear O/L /lighted switch/6' cord  
Part No. J06B0B



Six rear outlets, lighted switch, 15A, 6' (1.8m) cord.  
Receptacle center-to-center 1 1/2" (38mm).

## Features & Benefits

Six rear 20A outlets, 6' (1.8m) cord. Receptacle center-to-center 1 1/2" (38mm).

## Specifications

### General Info

|                       |  |                    |              |
|-----------------------|--|--------------------|--------------|
| Product Line          | Wiremold   | UPC Number         | 786776043884 |
| Country Of Origin     | Mexico   | Receptacle Type    | Simplex      |
| Number of Receptacles | 6  | Application Sector | Commercial   |
| Standard              | cULus Recognized: File E66421, Guide XBYS2 XUHT2 VZCA2 | Type               | PIOC         |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.75 in | Product Depth US | 2.57 in |
| Product Length US | 19.0 in |                  |         |

### Buy American Act Compliance

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

### Additional Information

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

---

## Technical Information

---

|                          |                        |                  |         |
|--------------------------|------------------------|------------------|---------|
| Phase                    | Single                 | Frequency Rating | 60 Hz   |
| Amperage                 | 15 A                   | Enclosure Type   | Steel   |
| Mounting Type            | Rack Mounting          | Voltage          | 125.0 V |
| Environmental Conditions | Dry interior locations |                  |         |

---