



Pass and Seymour  
LS Series CFL/LED/Incandescent Single Pole Slide Dimmer, Non-Preset, Ivory  
Part No. LSCL450I



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

## Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)	Works with dimmable CFL/LED or Incandescent lighting loads at 450W CFL/LED & 700W Incandescent
Built-in electromagnetic and radio-frequency interference protection	No dirt-catching crevices
Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plates available for all models	Preset ON/OFF switch automatically returns controlled lights to preset level without re-adjusting dimmer setting
Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts	Superior heat management
Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer	Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Features	Locator Light
Switch Type	Slider	Number of Switches	1
Application Sector	Residential	Standard	cULus, RoHS
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

### Dimensions

---

Product Width US 1.74 in

Product Depth US 1.28 in

---

Product Height US 4.19 in

---

### Technical Information

---

Frequency Rating 120VAC 60 Hz

Connection Screw Terminals

---

Bulb Compatibility CFL, Incandescent, LED

Number of Poles Single Pole

---

Wattage 700 W

Voltage 120.0 V

---

Load LED, Incandescent, CFL

Environmental Conditions Humidity: Less than 95% non condensing

---