



Pass and Seymour

LS Series CFL/LED/Incandescent Single Pole/3-Way Slide Dimmer with Single Pole/3-Way, 3-Speed De-Hummer Fan Control, Preset, Ivory

Part No. LSCLDC163PI



The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

## Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)

Single pole/3-way versions

Unique integrated single pole/3-way dimmer with fan speed control

Ratings: 150W LED & CFL: 300W Incandescent: 1.6A (Fan Control): 120VAC 60Hz

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Features	Combination, Fan Control, Locator Light
Switch Type	Push, Slider	Number of Switches	2
Application Sector	Residential	Standard	RoHS
Warranty Type	Limited Lifetime Warranty		

### Dimensions

Product Width US	2.5 in	Product Depth US	1.28 in
Product Height US	4.19 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Connection	Back & Side Wired	Contact Rating	120VAC
Amperage	1.6 A	Bulb Compatibility	CFL, Incandescent, LED
Number of Poles	3-Way, Single Pole	Wattage	300 W
Speed Range	3-Speed	Voltage	120.0 V
Environmental Conditions	Indoor Only		