



Pass and Seymour
LS Series Fan Speed/Dimmer Control, Black
Part No. LSDC16BKV

Dual Slide 3-Speed De-Hummer Fan Control with Single-Pole Dimmer



Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Device comes with wired leads.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Application Sector	Residential
Standard	UL Listed	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	109655	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Operating Cycles	100000	Amperage	1.6 A
Number of Poles	Single Pole	Wattage	300 W