



Pass and Seymour
LS Series Fan Speed Control/Dimmer, Ivory
Part No. LSDC16IV



Dual Slide 3-Speed De-Hummer Fan Control with Single-Pole Dimmer

Features & Benefits

- Tough impact-resistant thermoplastic housing.

Superior heat management: no time wasting break off tabs.

Can be used with patented Snap-In Light Module (sold seperately).
- Power-failure memory.

Device comes with wired leads.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Residential
Standard	UL Listed	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	109655	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Operating Cycles	100000	Amperage	1.6 A
Number of Poles	Single Pole	Wattage	300 W