



Pass and Seymour
LS Series Fan Speed Control/Dimmer, Light Almond
Part No. LSDC16LAV



Dual Slide 3-Speed De-Hummer Fan Control with Single-Pole Dimmer

Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Device comes with wired leads.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential	Standard	UL Listed
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	109655	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Operating Cycles	100000	Amperage	1.6 A
Number of Poles	Single Pole	Wattage	300 W