



Pass and Seymour
LS Series Dual Fan Speed Control/Dimmer, Ivory
Part No. LSDV25IV



Variable Speed Fan Control with Single-Pole Dimmer, 300W

Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Device comes with wired leads.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|-------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Country Of Origin | China | Application Sector | Residential |
| Standard | UL Listed | Type | Dimmer |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 109655 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|------------------|-------------|----------|-------|
| Operating Cycles | 100000 | Amperage | 2.5 A |
| Number of Poles | Single Pole | Wattage | 300 W |