



Pass and Seymour  
LS Series Fan Speed Control, White  
Part No. LSSC5PW

Decorator Slide Fan Control, Preset/3-Speed/5A



## Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive screw-pressure-plate back wire terminals eliminates wire nuts.

Can be used with patented Snap-In Light Module (sold separately).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Residential
Standard	UL Listed	Type	Dimmer

### Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.185 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Operating Cycles	100000	Amperage	5 A
Number of Poles	Single Pole	Voltage	120.0 V