



radiant Collection
radiant® Single Pole/3-Way Switch with Night Light, Nickel
Part No. NTL873NICC6



Add the convenience of a little extra light, wherever your home needs it, with this combination switch and built-in night light from the radiant® Collection. Easily replacing an existing single-pole or 3-way switch, the night light portion has five adjustable light levels and uses a hidden sensor to turn on when it is dark, making it a great addition to bathrooms, kitchens and nurseries. Features the sleek, clean lines of radiant for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any single-pole or 3-way switch with ease, in as little as 10 minutes. Offers installation flexibility, working in both single-pole and 3-way applications.

Features five adjustable light settings: Ultra Low, Low, Medium, High and OFF.

Hidden sensor controls night light based on ambient light, automatically turning on when it is dark.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
Country Of Origin	China	Features	Nightlight
Switch Type	Push	Number of Switches	1
Application Sector	Residential	Standard	cULus, UL Listed
Warranty Type	1-Year Limited Warranty	Type	Nightlight

Dimensions

Product Width US	1.29 in	Product Depth US	1.3 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140597	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Contact Configuration	15A	Operating Cycles	50000
-----------------------	-----	------------------	-------

Contact Rating	120	Number of Gangs	1
----------------	-----	-----------------	---

Amperage	15 A	Number of Poles	3-Way, Single Pole
----------	------	-----------------	--------------------

Mounting Type	Box	Voltage	120.0 V
---------------	-----	---------	---------

Environmental Conditions	UL94 V2		
--------------------------	---------	--	--
