



The 8"" in-ceiling model offers the highest power handling and performance with Titanium tweeters and combination Carbon Fiber/Kevlar woofers. This speaker has a super clean look and is finished beautifully with a completely rimless, magnetic grill. They offer quick and secure installation by utilizing three dog legs, instead of the usual four, and includes pivoting tweeters. There is also a tweeter level adjustment switch to tailor the tweeter output level. These tweeters are connected to a unique tweeter bridge that maximizes sound quality, looks great, and serves as a handle to hold the speaker by during installation.

## Features & Benefits

+/- 3dB Tweeter Level Output adjustment	8 ohm rated
Designed to perform for a lifetime	Grant better at home listening through quality design and materials
Magnetic rimless and paintable grill	Pivoting tweeter
Three dog leg design for easy installation	Unique tweeter bridge that also doubles as an installation handle

## Specifications

### General Info

Product Line	Nuvo	UPC Number	701963858959
Country Of Origin	China	Application Sector	Residential
Standard	CE, RoHS, REACH Compliant		

### Technical Information

Wattage	9.69 W	Impedance	8.0 ohms
Decibels	86 dB		