



Nuvo
Discontinued - 5.25 in Nuvo DVC Outdoor Speaker, White
Part No. NV6OD5DVCWH



Fill your outdoor space with crystal-clear, powerful audio using the Nuvo Series Six 5.25" Dual Voice Coil Outdoor Speaker. Offering the highest power handling and performance, this speaker is designed with a dual voice coil 5.25" combination carbon fiber/Kevlar woofer and two 1" titanium tweeters for the ultimate listening experience. The sleek enclosure boasts a modern form and minimal size that tastefully blend with the lines of any home.

Optimized for the demands of outdoor installations, the Outdoor Speaker is IP65 and MIL-STD- 810 rated. Designed for easy installation, the speaker safely rests on the bracket with mounting knobs loosely installed to allow flexibility while wiring the removable phoenix connector. After the terminal has been secured, simply adjust the angle, tighten knobs, install covers, and mounting is complete.

Features & Benefits

8 ohm rated	Aluminum powder coated grill
Aluminum speaker bracket	Designed for safe and easy installation
Fill your outdoor space with crystal-clear, powerful audio	IP65 Rated for outdoor use and MIL-STD-810 for UV, salt spray, and temperature extremes
Lifetime Warranty	Single stereo speaker is ideal when space is limited or two speakers aren't required
Output Wattage of 12.9 - 15.6	

Specifications

General Info

Product Line	Nuvo	Replaced by Part Number	NV6OD6DVCWH, NV6OD6DVCWH
UPC Number	701963859727	Country Of Origin	China
Application Sector	Residential	Standard	CE, RoHS, REACH Compliant, #ABS and #4 PELD Recyclable, IP65, MIL 810

Technical Information

Frequency Response	65 to 20 KHz	Maximum Wattage	3 W
--------------------	--------------	-----------------	-----

Wattage	10.2 W	Impedance	8.0 ohms
---------	--------	-----------	----------
