



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification.

Features & Benefits

- Up to 72 LC fibers per RU
- Made of durable polycarbonate
- 6, 8, 12 & 24 port panels
- Available in, LC, SC, ST and blank styles
- Zirconia ceramic sleeves for optimal performance
- Color options available

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875593799	Country Of Origin	Mexico
Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements.	Type	Adapter

Dimensions

Product Width US	5.12 in	Product Depth US	1.15 in
Product Height US	1.19 in		

Additional Information

Product Environmental Profile Yes

Technical Information

Ferrule	Zirconia Ceramic	Number of Fibers	12 Fibers
Fiber Type	Single-Mode	Form Factor	LC Duplex