

Series 18 In Line Connectors - fivefemale



## Features & Benefits

Interchangeable with Canadian CAM devices from other manufacturers. Ball nose design achieves NEMA 3R, 4 rating. Designed specifically for Sea Way cable. Accepts #6 through 4/0 size wire. Double set screws for premium wire retention. Locking screw prevents contact from rotating inside housing.

## Specifications

### General Info

|                   |                 |                    |                       |
|-------------------|-----------------|--------------------|-----------------------|
| Product Line      | Pass & Seymour  | Color              | White                 |
| Country Of Origin | Mexico          | Application Sector | Commercial/Industrial |
| Standard          | UL, cUL, cCSAus |                    |                       |

### Dimensions

|                   |        |
|-------------------|--------|
| Product Length US | 6.8 in |
|-------------------|--------|

### Technical Information

|           |       |                 |             |
|-----------|-------|-----------------|-------------|
| Amperage  | 400 A | Number of Poles | Single Pole |
| Wire Size | 2/0   | Voltage         | 600.0 V     |

|                          |  |
|--------------------------|--|
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |
|--------------------------|--|