



Series 18 In Line Connectors - Male

## Features & Benefits

Interchangeable with Canadian CAM devices from other manufacturers. Ball nose design achieves NEMA 3R, 4 rating. Designed specifically for Sea Way cable. Accepts #6 through 4/0 size wire. Double set screws for premium wire retention. Locking screw prevents contact from rotating inside housing.

## Specifications

### General Info

|                   |                 |                    |                       |
|-------------------|-----------------|--------------------|-----------------------|
| Product Line      | Pass & Seymour  | Color              | Green                 |
| Country Of Origin | Mexico          | Application Sector | Commercial/Industrial |
| Standard          | UL, cUL, cCSAus |                    |                       |

### Dimensions

|                   |          |
|-------------------|----------|
| Product Length US | 6.875 in |
|-------------------|----------|

### Technical Information

|                          |  |                 |             |
|--------------------------|--|-----------------|-------------|
| Amperage                 | 400 A  | Number of Poles | Single Pole |
| Wire Size                | 2/0  | Voltage         | 600.0 V     |
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |                 |             |