



Series 18 In Line Connectors - fivefemale

## Features & Benefits

Interchangeable with Canadian CAM devices from other manufacturers. Ball nose design achieves NEMA 3R, 4 rating. Designed specifically for Sea Way cable. Accepts #6 through 4/0 size wire. Double set screws for premium wire retention. Locking screw prevents contact from rotating inside housing.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Green
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL, cUL, cCSAus		

### Dimensions

Product Length US	6.8 in
-------------------	--------

### Technical Information

Amperage	400 A	Number of Poles	Single Pole
Wire Size	6 - 2 AWG	Voltage	600.0 V

Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4
--------------------------	--