



Pass and Seymour  
Medium Duty, Standard Length, Flexible Eye, T-Type  
Part No. PM0752



Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 0.750-0.990-inch, Mesh Length - 36-inch, Eye Diameter - 1/4-inch, Break Strength - 6,800 lbs.

## Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 36: Eye Diameter: 1/4

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Technical Information

Maximum Cable Range	0.75 in	Minimum Cable Range	0.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 6800		