

Medium Duty, Short Length, Flexible Eye, T-Type. Cable Diameter - 2.500-2.990", Mesh Length - 24", Eye Diameter - 1/2", Break Strength - 24,500 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Specifications

General Info

UPC Number 785007185546

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Construction Various Types of Pulling, Support and Strain Relief Grips

Standard UL/CSA Approval (consult factory)

Technical Information

Mounting Consult the Factory for Mounting Recommendations

Cable Size Cable Dia. Range: 2.500-2.990; Mesh Length: 24; Eye Diameter: 1/2

Capacity Various Cable Diameter Ranges

Load Approx. Break Strength: 24,500