



Pass and Seymour
Medium-Duty, Long Length, Flexible Eye
Part No. PM2503

Medium-Duty, Long Length, Flexible Eye. Cable Diameter - 2.500-2.990-inch, Mesh Length - 48-inch, Break Strength - 25,900 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 48

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	2.5 in	Minimum Cable Range	2.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 25900		