



Pass and Seymour
Medium Duty, Short Length, Flexible Eye, T-Type
Part No. PM3501



Medium Duty, Short Length, Flexible Eye, T-Type. Cable Diameter - 3.500-3.990-inch, Mesh Length - 26-inch, Eye Diameter - 5/8-inch, Break Strength - 31,000 lbs.

Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 26: Eye Diameter: 5/8

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	3.5 in	Minimum Cable Range	3.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 31000		