



Pass and Seymour
Medium Duty, Standard Length, Flexible Eye, T-Type
Part No. PM3502

Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 3.500-3.990-inch, Mesh Length - 40-inch, Eye Diameter - 5/8-inch, 31,000 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 40: Eye Diameter: 5/8

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Support and Strain Relief Grips, Various Types of Pulling | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 3.5 in | Minimum Cable Range | 3.99 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 31000 | | |