



Pass and Seymour
Heavy Duty, Short Length, Rotating Eye, K-Type
Part No. PS0501

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 0.500-0.610-inch, Mesh Length - 11-inch, Eye Diameter - 7/8-inch, Break Strength- 5,600 lbs.



Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 11: Eye Diameter: 7/8

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Various Types of Pulling, Support and Strain Relief Grips | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 0.5 in | Minimum Cable Range | 0.61 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 5600 | | |