

Heavy-Duty, Standard Length, Rotating Eye, K-Type. Cable Diameter - 1.000-1.490", Mesh Length - 33", Eye Diameter - 1 3/8", Break Strength - 16,400 lbs.



Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel. They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Specifications

General Info

UPC Number 785007994384

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Construction Various Types of Pulling, Support and Strain Relief Grips

Standard UL/CSA Approval (consult factory)

Technical Information

Mounting Consult the Factory for Mounting Recommendations

Cable Size Cable Dia. Range: 1.000-1.490; Mesh Length: 33; Eye Diameter: 1-3/8

Capacity Various Cable Diameter Ranges

Load Approx. Break Strength: 16,400