

Double pole, Triple wire, Non-Fusible Mechanical Interlock Receptacle. 30 amp, 120 vac.



Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Color Gray

UPC Number 785007421125

Countries Of Origin United States

Product Line Pass & Seymour

Application Sector Industrial

Standard UL Listed

Technical Information

Number of Poles Double Pole

Voltage 120 V

Phase 3

Number of Wires 3