



Canadian 3way Switch, Back & Side Wire, 20amp 347volt, Gray

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see www.legrand.us/patents.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Application Sector | Residential/Commercial |
| Standard | UL 20 | | |

Technical Information

| | | | |
|----------|--------|----------------|---------------|
| Actuator | Toggle | Contact Rating | 20amp, 347vac |
|----------|--------|----------------|---------------|

| | | | |
|----------|------|--------|------|
| Amperage | 20 A | Action | DPDT |
|----------|------|--------|------|

| | | | |
|-----------------|-------------|---------|---------|
| Number of Poles | Double Pole | Voltage | 347.0 V |
|-----------------|-------------|---------|---------|
