



Pass and Seymour
Heavy Duty, Short Length, Rotating Eye, K-Type
Part No. PS4001

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 4.000-4.490-inch, Mesh Length - 33-inch, Eye Diameter - 1 7/8-inch, Break Strength - 48,000 lbs.



Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 33: Eye Diameter: 1-7/8

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	4 in	Minimum Cable Range	4.49 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 48000		