



Pass and Seymour  
Pin & Sleeve Watertight 20A 3ø 250V Receptacle  
Part No. PS420R9W



Triple-Pole, 4-Wire, Pin and Sleeve Receptacle. 20A, 3/250V.

Features & Benefits

- All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.
- North American products come completely ready to wire, for quick, simple installation.
- And all feature chemical-resistant thermoplastic construction.
- Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.
- An exclusive, hinged cord grip eliminates loose parts that get lost.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Commercial
Standard	UL Listed		

Dimensions

Product Width US	3.2 in	Product Height US	3.8 in
Product Length US	3.5 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	151348	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Wires	4	Amperage	20 A
Number of Poles	3-Way	Wire Size	2 AWG
Voltage	250.0 V		