



Replacement Connector Front Body, 4-Wire 60A 3-Phase 250V.

## Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

North American products come completely ready to wire, for quick, simple installation. And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed

### Dimensions

Product Width US	4.5 in	Product Depth US	10.9 in
Product Height US	4.7 in		

### Technical Information

Number of Wires	4	Amperage	60 A
Number of Poles	3-Way	Voltage	250.0 V