



**Legrand**  
Non-Fusible Mechanical Interlock  
Part No. PS460MIR7W



Triple pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 60 amp, 3, 480 vac.

### Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

### Specifications

#### General Info

Color Gray

UPC Number 785007420586

Countries Of Origin United States

Product Line Pass & Seymour

Application Sector Commercial

Standard UL Listed

#### Technical Information

Number of Poles 3-Way

Voltage 480 V

Phase 3

Wire Size 2Awg

Number of Wires 4